




PRODUCT TYPE EC*U

Double Compression Barrier Gland designed for use with unarmoured cable featuring Peppers T2000 or T1000 Compound

Ex db : Ex eb : Ex nR : Ex ta : IP66 : IP68 : IP69



PART NUMBERS:

EC	1	U	B
	2		S

New Product



PRODUCT DESCRIPTION

"EC*U" type glands are certified Flameproof Ex db, Increased Safety Ex eb, Restricted Breathing Ex nR and Dust Protected Ex ta. They are suitable for use in Group I Mining, Zone 1 and 2 for Gas Groups IIA, IIB and IIC and additionally for use in Zones 20, 21 and 22 for Dusts Groups IIIA, IIIB and IIIC. Occasionally referred to as "potting glands", they provide a compound barrier Ex db & IP seal on the cable inner cores, eliminating damage to cables that exhibit "cold flow" characteristics and an additional environmental seal on the outer sheath. The unique features include, Peppers T1000 or T2000 compound that enables a quick and easy installation. An innovative barrier chamber that allows for a full inspection of the compound fill. The gland maintains IP66, IP68 to 100 metres and IP 69. Is deluge proof without the use of an additional seal or deluge boot. It is supplied with an IP O-ring seal as standard on metric entry threads.

COMPLIANCE STANDARDS:

EN 60079-0, EN 60079-1, EN 60079-7, EN 60079-15, EN 60079-31
IEC 60079-0, IEC 60079-1, IEC 60079-7, IEC 60079-15, IEC 60079-31 & IEC 60529

CERTIFICATION:

ATEX I M2 II 2G Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex ta IIIC Da II 3G Ex nR IIC Gc
IECEx Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex ta IIIC Da / Ex nR IIC Gc

CERTIFICATION No:

ATEX CML 19ATEX1113X & CML 19ATEX4114X
IECEx IECEx CML 19.0035X

EXAMPLE PART NUMBERING: EC2-UB/NP/20/M20

EC	Eclipse style barrier gland for use with Peppers T1000 or T2000 compound
2	Peppers T1000 (1) - Peppers T2000 (2)
U	Gland featuring double compression compound (Barrier) Inner Seal & Silicone Elastomeric Outer Seal for use with unarmoured cable
B	Brass (B) / Stainless Steel (S)
C	PVC Shroud (C) - PCP Shroud (P) - LSOH Shroud (3)
K - V - H	Locknut & Nylon (K), Fibre (V) or PTFE (H) IP Washer
T	Including Earth Tag
S	Including Serrated Washer
1	Quantity per kit
NP	Nickel Plated
20	Gland shell size
M20	M20 Entry Thread

OPTIONAL ACCESSORIES:

LOCKNUT	Brass (ACBLN) / Stainless Steel (ACSLN)
EARTH TAG	Brass (ACBET) / Stainless Steel (ACSET)
IP WASHERS	Nylon (ACNSW) / Fibre (ACFSW) / PTFE (ACPSW)
SERRATED WASHERS	Stainless Steel (ACSSW)
SHROUDS	PVC (ACSPVC) / PCP (ACSPCP) / LSOH (ACSSIO)

IP RATING:	IP66 & IP68 (100 metres - 7 days) & IP69
OPERATING TEMP:	T1000: -60°C to +135°C T2000: -60°C to +120°C
MATERIALS:	Brass or Stainless Steel
PLATING:	Electroless Nickel
COMPOUND:	Peppers T-1000 Compound / Peppers T-2000 Compound
OUTERSEAL:	Silicone LSOH

Eclipse featuring the New T2000 Compound

- Hand operated No Mixing VMS Cartridge
- Fast setting compound. Conductor termination can be effected from 60 minutes @ 23°C
- Featuring Peppers unique "no ferrule" technology allowing it to be fully retractable and inspectable
- Robust Compound for extreme conditions
- Deluge proof without the requirements of additional seals or boots
- Built in interface seal with metric threads

CABLE GLAND SELECTION TABLE (ALL DIMENSIONS IN mm)

Gland size	Entry Thread Size		Metric Thread Length [B]	Gland Sealing Range - Cable Sheath & Cores						Nominal Protrusion Length [L]	Dimensions/Weight (Metric)			Shroud Size (Metric)
	Metric	NPT		Cable Inner Sheath [C]			Cable Outer Sheath [D]				Across Flats [A]	Across Corners	Weight (Kgs)	
				Max Number of Cores [C] [T1000]	Max Number of Cores [C] [T2000]	Max Ø Over Cores [C]	Min Inner Sheath [T2000]	Min	Max					
16S	M16 x 1.5	3/8"	16	12	12	8.9	4.0	3.4	8.4	71.10	25.4	28.0	0.159	EL24
16	M20 x 1.5	1/2"	16	15	15	10.4	4.0	3.4	8.4	71.10	25.4	28.0	0.174	EL24
20S	M20 x 1.5	1/2" or 3/4"	16	35	15	10.4	4.0	4.8	11.7	72.10	25.4	28.0	0.175	EL24
20	M20 x 1.5	1/2" or 3/4"	16	40	20	12.5	4.0	9.5	14.0	70.95	30.0	33.0	0.223	EL30
25	M25 x 1.5	3/4" or 1"	16	60	30	16.5	8.0	11.7	18.5	76.05	37.6	41.4	0.347	EL38
32	M32 x 1.5	1" or 1 1/4"	16	80	50	23.5	14.0	18.1	26.3	79.60	46.0	50.6	0.523	EL46
40	M40 x 1.5	1 1/4" or 1 1/2"	16	130	65	28.8	16.0	22.6	32.2	79.20	55.0	60.5	0.725	EL55
50S	M50 x 1.5	1 1/2" or 2"	16	200	100	34.2	20.0	28.2	38.2	93.43	65.0	71.5	1.108	EL65
50	M50 x 1.5	2"	16	400	100	39.4	20.0	33.1	44.1	90.52	65.0	71.5	1.046	EL65
63S	M63 x 1.5	2" or 2 1/2"	19	400	130	44.8	30.0	39.3	50.1	91.65	80.0	88.0	1.467	EL80
63	M63 x 1.5	2 1/2"	19	425	130	50.0	30.0	46.7	56.0	88.75	80.0	88.0	1.398	EL80
75S*	M75 x 1.5	2 1/2" or 3"	19	425	-	55.4	-	52.3	62.0	94.74	90.0	99.0	1.783	EL90
75*	M75 x 1.5	3"	19	425	-	60.8	-	58.0	68.0	91.74	90.0	99.0	1.687	EL90
80*	M80 x 2.0	3" or 3 1/2"	25	425	-	64.4	-	61.9	72.0	112.55	104.7	115.2	2.969	EL104
85*	M85 x 2.0	3" or 3 1/2"	25	425	-	69.8	-	69.1	78.0	109.75	104.7	115.2	2.526	EL104
90*	M90 x 2.0	3 1/2" or 4"	25	425	-	75.1	-	74.1	84.0	107.35	114.3	125.7	3.008	EL114
100*	M100 x 2.0	3 1/2" or 4"	25	425	-	80.5	-	81.8	90.0	109.35	114.3	125.7	2.544	EL114

NOTES

- * Size 75S and above only available with T1000 Compound
- Gland size does not necessarily equate to the entry thread size.
- The IP O-ring seal is only available on metric entry threads. IP washers can be supplied for tapered entry threads
- Dimensions (A) & (B) may differ for glands with non metric entry threads. Please refer to our "Thread Reference Tables" for specific dimensions.
- Assembly instructions must be read prior to installation and adhered to in full.
- Peppers supplies cable glands with parallel entry threads that conform to the flameproof threaded joint requirements of IEC/EN 60079-1 and other equivalent standards. They usually incorporate a thread run out according to general machining techniques and parts will not have a full form thread for the entire length. Peppers Cable Glands Limited will not be held responsible for clients' installations where this has not been taken into account.
- When selecting IP Washer & Shroud material for use with glands, please be aware of the accessories temperature range to ensure they are suitable for the intended installation.
- The gland is supplied with the correct amount of compound, gloves and instructions to allow one complete termination